

Contents:

4-5
6-7
8
9
10
11
13
14
15

Electronics in healthcare

Electronics are permeating more and more into the healthcare sector, and electronics technology advances continue to enhance the functionality of healthcare equipment.

Murata is at the cutting edge of these electronics advancements and is a key provider of technologies which will help to shape the future of healthcare around the world. Apart from our standard products, which are present in almost any electronic equipment you use, Murata has developed new, innovative products specifically for healthcare applications. In this brochure we outline just a few of these innovations.



Please note that Murata does not support the usage of Murata's standard products for safety-critical applications that require especially high reliability.

Please don't hesitate to contact us if you have any questions or concerns.

MEMS HR sensor node

Non-contact heart rate and other cardiac measurement parameters

Electronic BCG (Ballistocardiography) module with accelerometer signal processing and algorithm in the on-board micro controller

Features

- A continuous contactless patient monitoring concept when in the bed
- Heart rate (HR), heart rate variability (HRV), respiration rate (RR) and bed occupancy detection can be utilized to analyze for example stress and relaxation index and sleep quality
- Opens new possibilities in patient monitoring and elderly care in hospitals, assisted living and at home.

Benefits


- Safety
- Efficiency
- Responsiveness



Learn about MEMS sensors

http://www.murata.com/en-eu/products/





MEMS sensors

High accuracy, low-power consumption

Murata is a leading supplier of acceleration, inclination and angular motion sensor solutions for healthcare applications.

Medical sensors increase the intelligence of life supporting devices, and they can be used in new types of patient monitoring applications that allow patients to lead more independent lives. Detecting signals triggered by symptoms helps optimize medication and prevent serious attacks of illness.

Murata's unique MEMS design, which combines single crystal silicon and glass, ensures exceptional reliability, unprecedented accuracy and excellent stability over time. The power requirements of these medical sensors are extremely low, which gives them a

significant advantage in small batteryoperated devices.

As the leading supplier of activity sensors for pacemakers Murata also offers a wide range of pressure sensors, accelerometers, inclinometers and gyroscopes for various demanding medical and healthcare applications. Device developers and manufacturers of many existing and emerging healthcare applications have been able to reach their power and size requirements thanks to Murata's MEMS technology.





Sensor Elements (Dies)

Vertical Accelerometer Elements SCG12S and SCG14S

- Size 3mm x 2.12mm x 1.95 or 1.25mm
- Various measuring ranges possible (1 12g)
- Proven capacitive 3D-MEMS Technology

Horizontal Accelerometer Elements SCG10X and SCG10Z

- Size SCG10X: 2.55mm x 2.95mm x 1.91mm
- Size SCG10Z: 1.50mm x 1.70mm x 1.83mm
- Various measuring ranges possible (1 12g)
- Proven capacitive 3D-MEMS Technology

Pressure Sensor Elements SCB10H

- Size 1.4mm x 1.4mm x 0.85mm
- High pressure shock survival (> 200 bar)
- Various pressure ranges possible (1.2 25 bar)
- Proven capacitive 3D-MEMS technology
- Operates at near vacuum applications

Sensor Modules

Accelerometer

Digital 1-, 2- or 3-axis Accelerometers

- Excellent accuracy
- Excellent stability over temperature
- Ranges: ± 2g, ± 6g

Inclinometer

Analog 1- or 2-axis Inclinometers

- Excellent accuracy
- Excellent stability over temperature
- Ranges: ± 15°, ± 30°, ± 90°



Gyroscope

1-axis Angular Rate Sensors

- Excellent accuracy
- Excellent stability and noise performance
- Ranges: ± 100 °/s , ± 300 °/s



Products for healthcare www.murata.com



Sensors / Thermistors

Sensors

Sensor product lineup

Pyroelectric Infrared Sensors

Ultrasonic Sensors

Magnetic Pattern Recognition Sensors

Magnetic Switches (AMR Sensors)

Shock Sensors

Angular Rate Sensors

Rotary Position Sensors

MEMS Sensors



Low profile, flexible with excellent responsiveness

NEW

Easily routed in complex designs the flexible film temperate sensor is ideal for sensing housing temperatures of compact devices as wearable healthcare products, smartphone and tablets.

This range of surface-mounted NTC temperature sensors are packaged on a flexible printed circuit (FPC) film and measuring at $50.00 \times 3.17 \times 0.55$ mm in size. The FTNT55XH103FA1A050 can measure temperatures in the range of -40 to + 125 degrees C and has an accuracy, at 25 degrees C of +/- 0.4 degrees C. Resistance at 25 degrees C is 10 k ohm +/- 1%.

The film temperature sensor has been granted 4 patents including 1 basic patent and 3 peripheral patents.

Features

- FPC thickness approximately 100µm for easy wiring in complex structures and tight spaces
- Equipped with low heat capacity making thermal responsiveness excellent

Learn more online

http://www.murata.com/en-eu/products



FTNT55XH103FA1A050

Thermistors

The tightest temperature tolerance chips and lead types covering inrush current suppression, temperature compensation, overcurrent and overheat sensing.

Learn more online

http://www.murata.com/en-eu/products. thermistor



Product lineup

PTC & NTC Thermistor

For overcurrent protection & temperature sensor / temperature compensation

Chip NTC Thermistor

For temperature sensor / temperature compensation

Chip PTC Thermistor Line-up

For overheat sensing / overcurrent protection

PTC Thermistor lead type



Connectivity modules

Connectivity modules Low-power reliable connectivity for healthcare devices

Healthcare devices are increasingly connected to each other and the web. Use a Murata module for proven RF excellence.

Murata RF modules make it easy for you to build connectivity into most devices, even those where space is limited and power consumption needs to stay low.

With **BLE (Bluetooth® Low Energy)** devices as small as 4.8 x 5.8 x 1.0mm, wireless communication has never been easier to design in.

Features

- Support BLE (Bluetooth® Low Energy), Bluetooth®, WiFi®, and other wireless standards
- Combo-modules available (Bluetooth®/WiFi®, etc.)
- Easy to design in
- Antenna matching supported

Applications

- E-health / home monitoring
- Connectivity of healthcare appliances like blood pressure meter, glucose meter, etc.



Learn more online

http://wireless.murata.com/eng/products/ wireless-connectivity-platforms.html



Wi-Fi™ 802.11b/g/n Murata WICED module portfolio



Product	Murata P/N	Chipset	Processor	WLAN	Op. Temp	Size (mm)	Host Interface	Antenna	Cert.	Grade
Type 1FX	LBWA1KL1FX-875	BCM43364	N/A	802.11b/g/n	-20°C to +75°C	6.95 x 5.15 x 1.1	SDIO	External	No	Consumer
	LBWA1ZVYDZ-679 (WICED SW)									
Type YD	LBWA1ZVYDZ-682 (Ayla SW)	Broadcom [®] BCM43362	STM32 ARM® Cortex®-M3	802.11b/g/n	-40°C to +85°C	10.0 x 7.9 x 1.25	UART/SPI	External	Yes	Consumer
	LBWA1ZVYDZ-739 (Murata SW)									
Type ZD	LBWA1ZVZDZ-681	Broadcom® BCM43362	STM32 ARM® Cortex®-M4	802.11b/g/n	-40°C to +85°C	10.0 x 7.9 x 1.25	UART/SPI	External	TBD	Consumer
Type ZX	LBWA17DZX6-705	Broadcom® BCM43362	N/A	802.11b/g/n	-40°C to +85°C	7.0 × 6.0 × 1.2	SDIO	External	No	Consumer
	LBWB1ZZYDZ-713 (WICED SW)									
Type YD- Certified	LBWB1ZZYDZ-683 (Ayla SW)	Broadcom® BCM43362	STM32 ARM® Cortex®-M3	802.11b/g/n	-40°C to +85°C	33.0 x 18.0 x 2.5	UART/SPI(MCU)	External	Yes	Consumer
	LBWB1ZZYDZ-740 (Murata SW)									


Products for healthcare www.murata.com

Connectivity modules



Wi-Fi[™] - Broadcom[®] chip set 2.4GHz IEEE 802.11b/g/n radio technology

Pi	oduct	Murata P/N	Chipset	Processor	WLAN	Op. Temp	Size (mm)	Host Interface	Antenna	Cert.	Grade			
c N	18000	88-00153-00	Broadcom®	N/A	802.11b/g/n	-40°C to +85°C	24.0 x 11.4	SDIO/SPI	On Board or	Yes	Industrial			
31		88-00153-02	BCM43362	IVA	002.11b/g/II	-40 C t0 +65 C	x 1.9		U.FL Connector	res	IIIdustriat			
C.	1820X	88-00158-00	Broadcom®	STM32 ARM®	002 115 /-/-	902 11b/c/p	902 11b/g/p	4000 to 0500	-40°C to +85°C 3	30.5 x 19.4	LIADT/CDI	On Board or	Yes	Industrial
31		88-00158-02	BCM43362	Cortex®-M3	002.11b/g/II	-40°C 10 +65°C	x 2.8 UART/SPI		U.FL Connector	res	muusmai			



Wi-Fi[™] 802.11a/b/g/n with Bluetooth 4.0[™] for Linux[™] & Android platforms

Product	Murata P/N	Chipset	WLAN	ВТ	Clock	Op. Temp	Size (mm)	Host Interface	Antenna	Cert.
Type ZP	LBEH5HMZPC	BCM4339	802.11 a/b/g/n,ac	BT®+BLE®	X'tal	-20°C to +75°C	7.8 × 7.42 × 1.0	SDIO(Wi-Fi™), UART(BT®)	External	No
Type 1BW	LBEH5DU1BW	Broadcom [®] BCM43340	802.11 a/b/g/n	BT®+BLE®	Internal X'tal	-20°C to +75°C	8.0 x 7.5 x 1.33	SDIO(Wi-Fi™) + UART(BT®)	External	No
Type 1DX	LBEE5KL1DX-875	BCM4343W	802.11b/g/n	EDR & BLE® v4.1	Internal X'tal	-20°C to +75°C	6.95 x 5.15 x 1.1	SDIO(Wi-Fi™) + UART(BT®)	External	Yes
Type XR	LBEP5CLXRC-701	TI WiLink™ 8 WL1801	802.11b/g/n	No	External	-40°C to +85°C	9.9 x 8.8 x 1.3	SDIO(Wi-Fi™)	External	No
Type WT	LBEP5CLWTC-601 (WLAN Only)	TI WiLink™ 8 WL1831 802.1	802.11b/g/n	v4.0 (BLE®+EDR)	Internal X'tal	-40°C to +85°C	199x88x13	SDIO(Wi-Fi™), UART(BT®)	External	No
	LBEP5CLWTC-631 (WLAN + BT + BLE)	WLIGGI		(BLL FLDR)		+03 C		OART(BT)		
Type WM	LBEP5CLWMC-603 (WLAN Only)	TI WiLink™ 8 WL1833	802.11a/b/g/n	v4.0 (BLE®+EDR)	Internal X'tal	-40°C to +85°C	9.9 x 8.8 x 1.3	SDIO(Wi-Fi™), UART(BT®)	External	No
	LBEP5CLWMC-633 (WLAN + BT + BLE)	WL1033	002.11d/b/g/II	(DLL +LDR)		+0.5 C		OART(BT)		



Bluetooth SMART® modules

Product	Freq	Murata P/N	Power Class	Version	Output Power	Op. Temp	Size (mm)	Host Interface	Antenna	Cert.
Type VZ	2.4GHz	LBCA2ZZVZZ-721 (Central Device) LBCA2ZZVZZ-722 (Peripheral Device)	Class 3	BLE [®]	-2dBm	-10°C to +60°C	20.0 x 13.0 x 24	UART	On Board	Yes
Type WS	2.4GHz	LBCA2ZXWSE-723 (Central Device) LBCA2ZXWSE-724 (Peripheral Device)	Class 3	BLE®	-2dBm	-10°C to +60°C	10.4 x 7.7 x 1.8	UART	External	Yes
Type ZF	2.4GHz	LBCA2BZZFZ	Class 3	BLE® v4.1	0dBm	-20°C to +85°C	5.4 x 4.4 x 1.0	UART	External	No
Type ZY	2.4GHz	LBCA2HNZYZ-711	Class 3	BLE® v4.1	0dBm	-20°C to +85°C	7.4 x 7.0 x 1.0	UART	Internal	Yes
Type 1BX	2.4GHz	LBMA15Q1BX	Class 1	BT®+BLE®	13dBm (Max)	-30°C to +85°C	5.0 x 4.5 x 1.0	UART	External	No

AC-DC front-end power supplies Medical approved

Custom products also available for medical applications

Selection table

	Series	Convection Cooling	Forced Air 250LFM	Input Voltage (Vac)	Output Voltage (V)	Efficiency
	MVAC400	250W	400W	90-264	12V/24V/50V	93%
	MVAC250	170W	250W	90-264	12V/24V/50V	93%
NEW	MVAD160	110W	160W	90-264	12V/24V/48V	93%
	MVAB120	75W	120W	90-264	12V/24V/28V/48V	91%
	MVAD065	65W	65W	90-264	12V/24V/48V	90%
	MVAD040	40W	40W	90-264	12V/24V/48V	89%

Features


- Universal input 90-264Vac
- Active power-factor correction
- Up to 250W natural convection cooling
- -20°C to +70°C full power operating temp.
- Class B conducted EMC
- Aux isolated 12V@1A fan output
- MVAC 250/400: 10W 5V standby power
- MVAD040/065: less than 0.3W at no load
- 2 x MOPP (Primary-Secondary)
- 1 x MOPP (Secondary-Chassis/Earth Enclosure

Quality/Safety

- 60601 (3rd edition) MOPP, 60950 safety approval
- 2 year warranty

Applications

Mains-powered medical equipment







Products for healthcare www.murata.com

DC-DC converters

Low power modules

Compact 1W & 2W DC-DC converter complies with UL60601-1

Industry standard, pin compatible 1W and 2W converters maintaining high levels of efficiency at light loads.



MEJ1 & MEJ2

Learn more online http://power.murata.com/en/products/ dc-dc-converters.html

Features

- High efficiency across the full load range
- Op. temp. range: -40° to 85°
- Encapsulated: superior thermal performance
- 72-79% typical efficiency
- 3.5 5% typical load regulation
- ANSI AAMI ES60601-1 recognition
- UL60950

Selection table

Series	Isolation	Input voltage	Output voltage	Efficiency	Power rating
MEJ1	5200Vdc	3.3/5/12/15/24V	3.3/5/9/12/15V	69-78%	1W
MEJ2	5200Vdc	3.3/5/12/15V	3.3/5/9/12/15V	70-82%	2W

Configurable output voltage, high isolation DC-DC converters

With configurable triple output voltages of +15V, +5V and +5V, the MGJ series of DC-DC converters is ideal for powering gate drives for IGBTs and Mosfets (standard, SiC) in bridge circuits . The MGJ series is characterised for high isolation and common mode dv/dt requirements. A disable/frequency synchronisation pin simplifies EMC filter design.

NEW MGJ3 & MGJ6

Features

- 3 outputs configurable for all gate drive applications: +15V/-5V, +15V/-10V & +20V/-5V outputs
- ANSI/AAMI ES60601-1 pending
- Reinforced insulation to UL60950 pending
- Characterised dv/dt immunity
- Characterised partial discharge immunity
- Ultra-low coupling capacitance 15pF
- Operation to 105°C

Configurations

Function	IGBT	SIC	MOSFET
15V Output	+15V	+20V	+15V
15V (OV reference) 5VA output	OV		OV
15VA (OV reference) 5VB output		OV	-5V
5VB (OV reference)	-10V	-5V	

Selection table		Output 1		Output 2			Output 3			
Setection tubte	Rated Output Voltage (V)	Rated Output Current (mA)	Output Power (W)	Rated Output Voltage (V)	Rated Output Current (mA)	Output Power (W)	Rated Output Voltage (V)	Rated Output Current (mA)	Output Power (W)	
MGJ3T05150505MC	15	120	1.8	5	120	0.6	5	120	0.6	
MGJ3T12150505MC	15	120	1.8	5	120	0.6	5	120	0.6	
MGJ3T24150505MC	15	120	1.8	5	120	0.6	5	120	0.6	
MGJ6T05150505MC	15	240	3.6	5	240	1.2	5	240	1.2	
MGJ6T12150505MC	15	240	3.6	5	240	1.2	5	240	1.2	
MGJ6T24150505MC	15	240	3.6	5	240	1.2	5	240	1.2	



Inductors

Murata chip inductors feature compact size and high-performance. The unique coil and case structures give them low DC resistance and outstanding highfrequency characteristics.

Murata offers a broad variety of products for different applications.

The diverse lineup offers the customer a choice of the types of inductors and characteristics optimal for the circuit in question.

Learn more online

http://www.murata.com/en-eu/product





Inductors for Power Circuits (Power and Choke)

RF Inductors



Power inductors

Inductors are passive components and are required in all noise-sensitive electronic power circuits. Magnetic inductors are not restricted by application.

Whether you need to reduce noise or protect vital components, we can offer a wide range of products to suit your requirements, having developed over 1,200 highly advanced and optimized inductor and transformer solutions. With an emphasis on miniaturization, reliability and ease of handling, our inductors, current transformers and common mode chokes are available in a variety of styles including bobbin, radial, axial and surface mount.

Learn more online

http://www.murata-ps.com/en/products/ magnetics.html






Power inductors

www.murata.com

Products for healthcare

EMI Noise suppression

Using Murata's ceramic processing technology and unique material, we offer a variety of Noise Suppression Products and EMI Suppression Filters. Murata also offers technical support and guidance based on many years of experience operating in the field of noise suppression.



Learn more online

http://www.murata.com/en-eu/products/ emc



Capacitors

Murata offers the No. 1 most abundant lineup in the industry, responding to all possible needs, and proposing ideal solutions.

Continuing to evolve as the world's No.1 manufacturer of monolithic ceramic capacitor

Learn more online

http://www.murata.com/en-eu/products capacitor



Product line-up

- Monolithic ceramic capacitors
- High voltage capacitors
- PAC (Polymer aluminum electrolytic capacitors)
- Film capacitors
- EDLC (Electrical double layer capacitors)
- Safety capacitors
- Trimmer capacitors
- Single layer microchip capacitor



EDLC, GRM, ZRB, TZC3

11

Timing Devices

Ceramic resonators (CERALOCK®) are made of high stability piezoelectric ceramics that function as a

With the advance of the IC technology, various equipment may be controlled by a single LSI integrated circuit, such as the one-chip microprocessor.

mechanical resonator.



Product line-up


Ceramic resonators

Ceramic filters

Crystal units

Crystal oscillators

Piezoelectric sound components



Timing devices

Crystal units



Since 2009, Murata's crystal unit has offered a compelling balance of value and accuracy, in an innovative 2016 package. Such features are ideal for size and cost conscience consumer, and communication applications.

Murata Crystal Unit Metal Cap Crystal Element Ceramic Plate

Conventional Crystal Unit

Metal or Ceramic Plate

Features

Small size

- 2016* size for 24MHz to 48MHz
- 2520* size for 16MHz to 24MHz

*2016 = 2.0mm x 1.6mm package size *2520 = 2.5mm x 2.0mm package size

Economical & robust design

- Simple structure using Murata's proven package technology
- · Particle screening process for enhanced reliability

RoHS Compliant & Pb Free

Crystal Element **Ceramic Cavity**

Frequency Tolerance

- Available +/-20ppm* for Consumer
- Available +/-100ppm* for Automotive

Learn more online http://www.murata.com/en-eu/protimingdevice/crystalu

Products for healthcare www.murata.com

12

Sound components

PKMCS0909E4000-R1

Sound components

Piezoelectric sound components utilize natural oscillation of piezoelectric ceramics. They are widely used in the applications from healthcare to consumer products.



Ultra compact light and low power SMD piezoelectric sounder suits portable healthcare devices

The smallest and lightest surface mount piezoelectric sounder available. Occupying significantly less surface area, and with a combined weight and area reduction of 44% compared to other similar products.

Specifications	
Sound pressure level	65dB min
Measure condition of sound pressure level	±1.5 Vo-p, 4.0kHz, square wave, 10cm
Maximum input voltage	±12.5Vo-p max
Operating temperature range	-40 to +85°C
Storage temperature range	-40 to +85°C
Drive type	External-drive

Features

- Small, thin and lightweight
- 9.0mm x 9.0mm x 1.9mm
 - 44% reduction of its predecessor
- Low power consumption 6.0Mv
- Noiseless piezo base enables minimum impact on surrounding circuitry by not getting any electrical noise


Applications

- Healthcare: Blood glucose meters, thermometers, etc.
- Consumer: Remote controls, mobile printers, digital cameras, etc.


Learn more online

http://www.murata.com/en-eu/
products/sound

Frequency Characteristics of Sound Pressure Level







Track, trace, & verify with ultra-miniature UHF RFID tags

Whether your focus is on anti-counterfeiting, inventory management, or process control, MAGICSTRAP® offers you an integrated solution with a tag size which can meet the challenges of almost any application.

At only 2.0×1.2 (LXMS21) and 3.2×1.6 (LXMS31), the **MAGICSTRAP®** UHF IC module is one of the smallest in the world. It can be mounted onto, or embedded into, a wide variety of materials even in non-electronic products, and can be surface-mounted directly onto your PCB for use in medical electronics.

In association with partner companies offering hardware & software solutions, we are able to provide a fully integrated system that gives you massive read/write functionality all built around an unbelievably small module.

Features

- RF circuitry incorporated in LTCC substrate
- Read range:
 - Up to 2cm using the component alone*
 - Up to 7m with external antenna
- Can be mounted on many surfaces
- Can be embedded into many materials
- Small SMD: 2.0 x 1.2 (LXMS21) and 3.2 x 1.6 (LXMS31)
- Complies with EPCglobal C1G2, ISO 18000-6C

*Loop type antenna for reader/writer is required





Applications

- Anti-counterfeit
- Process control/traceability of medical electronics
- Tracking/tracing PCBs
- Inventory management in healthcare institutions
- Probe tracking

Small Size

2.0 x 1.2 (LXMS21) or 3.2 x 1.6 (LXMS31), surface-mounted device





14

my Murata

Find what you need, when you need it

The new 'my Murata' portal is designed to respond to your individual needs. This space acts as a conference room in which you and Murata can meet.

Focused on products and solutions, this service provides you with the information you need - quickly. Our aim is to make you will feel like you have a Murata salesman or engineer at your side.



Get the latest product information

You can find out about the latest ceramic capacitor product lines, updated regularly as well as some unreleased product information, exclusively available on 'my Murata'. Plus much more...






'my Murata' knowledge exchange

To get feedback from the engineering community post your questions onto the 'Forum' which is provided to allow customers with similar experiences to exchange ideas and knowledge through discussions with Murata engineers. Find product specifications, mounting know-how, noise suppressions solutions, plus much more...



Enhanced design tool

Simulate the characteristics of Murata products using the enhanced version of our 'SimSurfing' software available on the 'my Murata' portal.



Global locations

For details please visit www.murata.com



Note



For customers outside Japan:

No Murata products should be used or sold, through any channels, for use in the design, development, production, utilization, maintenance or operation of, or otherwise contribution to (1) any weapons (Weapons of Mass Destruction [nuclear, chemical or biological weapons or missiles] or conventional weapons) or (2) goods or systems specially designed or intended for military end-use or utilization by military end-users.

For customers in Japan:

For products which are controlled items subject to the "Foreign Exchange and Foreign Trade Law" of Japan, the export license specified by the law is required for export.

- 2 Please contact our sales representatives or product engineers before using the products in this catalog for the applications listed below, which require especially high reliability for the prevention of defects which might directly damage a third party's life, body or property, or when one of our products is intended for use in applications other than those specified in this catalog.
 - Aircraft equipment
 - Aerospace equipment
 - 3 Undersea equipment
 - Power plant equipment
 - Medical equipment
 - Transportation equipment (vehicles, trains, ships, etc.)
 - Traffic signal equipment
 - (8) Disaster prevention / crime prevention equipment
 - Data-processing equipment
 - Application of similar complexity and/or reliability requirements to the applications listed above

- 3 Product specifications in this catalog are as of March 2014. They are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. If there are any questions, please contact our sales representatives or product engineers.
- 4 Please read rating and \(\Delta\)CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
- 5 This catalog has only typical specifications.
 Therefore, please approve our product
 specifications or transact the approval sheet
 for product specifications before ordering.
- Please note that unless otherwise specified, we shall assume no responsibility whatsoever for any conflict or dispute that may occur in connection with the effect of our and/or a third party's intellectual property rights and other related rights in consideration of your use of our products and/or information described or contained in our catalogs. In this connection, no representation shall be made to the effect that any third parties are authorized to use the rights mentioned above under licenses without our consent.
- 7 No ozone depleting substances (ODS) under the Montreal Protocol are used in our manufacturing process.

Murata Manufacturing Co., Ltd.

www.murata.com

